

FS-500 Series – Low Cost Units for Threaded Plastic Piping

Flow Rate Settings: 0.25 GPM to 5.0 GPM Port Size: 3/4" NPT Primary Construction Material: Polypropylene Setting Type: Fixed

The FS-500 offers low cost flow monitoring with a variety of switch actuation points and low pressure drop. All wetted parts are polypropylene or stainless steel, making this switch ideal for a wide range of chemical and temperature requirements. These Flow Switches can be used in water treatment applications including chlorinators, purifiers and heaters. The FS-500 is ideal for equipment cooling including welders, lasers, etc. A J-box version with a 5 amp relay is also available for direct control of higher electrical loads, such as chlorinator pumps.



Specifications

Wetted Materials* Housing, Bonnet, Shuttle, Shuttle Cap	Polypropylene, Hydrolytically Stable	
0-Ring	Viton [®] or Buna N	
Spring	316 Stainless Steel	
Retaining Clip	PH 15-7 Mo Stainless Steel	
Operating Pressure, Maximum	100 PSIG (6.9 bar) @ +70°F (21°C)	
	50 PSIG (3.4 bar) @ +180°F (82°C)	
	40 PSIG (2.8 bar) @ + 212°F (100°C)	
Operating Temperature, Maximum	0° to 212°F (100°C)	
Set Point Accuracy	± 20%	
Set Point Differential	± 20% Maximum	
Switch**	SPST, N.O. Pilot Duty 20 VA, 120-240 VAC or VDC	
J-Box with 5A Relay		
Coil	120 VAC 50/60 Hz	
Contacts SPDT	5A – 240 VAC Res	
	1/3 HP – 120 VAC	
	5A – 28 VDC Res.	
Inlet/Outlet Ports	3/4″ Female NPT	
Electric Termination		
Pilot	No. 22 AWG, 24" Zip Cord Lead Wires	
J-Box	6' PVC Cable	

**See "Electrical Data" on Page X-5 for more information.


How To Order – Standard Models

Specify Part Number based on switch actuation set point. Set points other than those listed are available as special order; contact GEMS with your requirements. Normally closed switch logic units available as special orders.


Switch Actuation Set Point	Part N	mbers	
GPM	Pilot Duty	J-Box w/5A Relay	
0.25	170231 🗲	175901	
0.50	170232 🗲	175902	
1.00	170233 🗲	—	
2.00	175117	_	
2.50	170234 🗲	_	
5.00	170235 🖌	_	

Note: Use of 100 micron filtration is recommended.

🗲 – Stock Items.



Dimensions



Pressure Drop - Typical

